


**Extensive Sleeve & Flange – 5-1/2" [140] to 9-7/8" [281] wall depth**

Healthcare Accessories

MasterFormat Section 10 28 13




Scan for Information



**SUSTAINABILITY/LEED**

MR 4.1 (1) MR 6 (1) EQ 4.2 (1)  
MR 4.2 (1) EQ 4.1 (1) EQ 4.4 (1)



**NOTE:**  
ALL DIM'S INCH [MM]  
ILLUSTRATION FOR REF ONLY AND NTS

**PRODUCT OVERVIEW**

Sleeve extends cabinet profile through wall to provide clear access to door. Door inside extension sleeve will only open 90° and will be returned by internal extension spring when released by user. Interlocked compartment doors will still preserve user privacy by preventing opening of opposite door until first door is fully closed in the same manner as the standard unit. Used with product 8154. Extension sleeve and flange for Recessed Specimen Pass-Through Cabinet. Sleeve slides over cabinet of Model #8154 in place of standard adjustable flange and does not prevent rear door from opening. Included with Model #8156

**KEY FEATURES & SPECIFICATIONS**

- Extensive Sleeve & Flange
- 22 Gauge Type 304 Stainless Steel, alloy 18-8 - Satin Finish
- Heavy duty stainless steel multi-staked 3/16" diameter [Ø5] piano hinge and is held
- 5-1/2" [140] to 9-7/8" [251]

**OPERATION & MAINTENANCE**

Sleeve extends cabinet profile through wall to provide clear access to door. Door inside extension sleeve will only open 90° and will be returned by internal extension spring when released by user. Interlocked compartment doors will still preserve user privacy by preventing opening of opposite door until first door is fully closed in the same manner as the standard unit.

**TECHNICAL INFORMATION / PRODUCT PROPERTIES**

Property	Value
Dimensions	13-1/4" [337] W x 12-3/4" [324] H x 6" [152] D
Construction	Type 304 Stainless Steel - Satin Finish
Mounting	Recessed
Capacity	N/A

**INSTALLATION**

Unit can be mounted through walls in the thickness range of 5-1/2" [140] to 9-7/8" [251]. Fixed flange and cabinet of Model #8154 is secured first through four (4) dimpled mounting holes that accommodate #10 self-threading Philips flat head (or oval head) screws (supplied). Adjustable extension sleeve & flange is then located to cabinet inside wall thickness and secured to opposite side of wall in same manner. For compliance with 2010 ADA Accessibility Standards, install unit with centerline of door pulls at 48" [1219] maximum Above Finished Floor (AFF). For general utility install unit with centerline of doors at 54" [1372] AFF.

Partition Cutout (PCO): 11-1/2" [292] W x 11" [279] H x 5-1/2" [140] to 9-7/8" [251] D

**WARRANTY**

One (1) Year from date of Invoice